


DO NOT SCALE

IF IN DOUBT -- ASK STANDARD_INSTALLATION



PUMP BOX SIZE
400l x 300w x 450h
ACCESS THROUGH
LID ON TOP

SITE

GATE

STEPLIFT

RAMP

H-FRAME

UNLESS SPECIFIED
DIM LIMITS ARE
MM NOMINAL

COATING:
MATERIAL:

DETAIL of CHANGE:

CHANGE NO.	DESIGNER	DATE
	PAUL MITCHELL	10-Aug-06
SUPERSEDES:		
INITIAL RELEASE.		

LIFT TYPE:	PLATFORM - 1000 RISE
LIFT WIDTH:	STD
LIFT DEPTH:	STD
HINGE SIDE:	RIGHT HANDED
MODEL NAME:	
QTY / LIFT:	

COPYRIGHT



UNIT: STEPLIFT

NAME: STANDARD INSTALLATION

STANDARD_INSTALLATION



SCALE 3:100

SHEET 1 of 2



PRO/ENGINEER DRAWING

DO NOT SCALE

IF IN DOUBT -- ASK STANDARD_INSTALLATION



* CLEARANCE EITHER SIDE OF STEPLIFT MUST BE < 10mm OR > 150mm TO COMPLY WITH BS6440.



UNLESS SPECIFIED DIM LIMITS ARE MM NOMINAL

COATING:		
MATERIAL:		
<i>DETAIL of CHANGE:</i>		
CHANGE NO.	DESIGNER	DATE
	PAUL MITCHELL	10-Aug-06
SUPERSEDES:		
INITIAL RELEASE.		

LIFT TYPE:	PLATFORM - 1000 RISE
LIFT WIDTH:	STD
LIFT DEPTH:	STD
HINGE SIDE:	RIGHT HANDED
MODEL NAME:	
QTY / LIFT:	
SCALE 1:50	SHEET 2 of 2

COPYRIGHT

UNIT: STEPLIFT

NAME: STANDARD INSTALLATION

STANDARD_INSTALLATION

PRO/ENGINEER DRAWING